

Tek-CARE[®] 500 Comparison Chart—FA to ES Devices

IL925 • Rev. 0 • 08/2011

Previous FA (Frequency Agile) Devices		Current ES (EchoStream) Devices	
NC500SK	Site Survey Kit	NC500ESSK	Site Survey Kit
NC501	Master Station Computer	NC501ES	Master Station Computer for Echostream transmitters
NC502	PC-Alarm Panel for Central Monitoring	NC502	PC-Alarm Panel for Central Monitoring
NC505	Additional Receiver (requires 1 PK505)	NC505ES	Remote LCD Receiver, 16 points/6 outputs (PK505 req)
		NC506ES	Remote Receiver, 4 points/4 outputs (requires PK505)
		NC507ES	Remote LCD Receiver, 12 outputs (requires PK505)
NC510	Receiver & Power Supply/PC Interconnect	NC510ES	NC510ES Receiver & Power Supply/PC Interconnect
NC511	Repeater	NC511ES	Repeater/Locator with backup battery
NC512	Locator		Locator function now part of the NC511ES
BA510	Backup Battery for NC511, NC512		NC511ES includes battery backup; NC512 is obsolete
PK250B	UPS for NC501	PK250B	UPS for NC501ES
IH511	IH511 Weatherproof Housing NC511, NC512, BA510	IH511	Weatherproof Housing for NC511ES
PK505	Transformer for NC505	PK505	Transformer for NC505ES, NC506ES, NC507ES
SF501	Water-Resistant Single Button Pendant Transmitter	SF501ES	Water-Resistant Single Button Pendant Transmitter
		SF501/2ES	Water-Resistant Dual Button Pendant Call Transmitter
SF502	Wall-Mounted Call Transmitter	SF502ES	Wall-Mounted Call Transmitter
SF505	Wireless Smoke Detector	SF505ES	Wireless Smoke Detector
SF515	Passive Infra-Red Motion Detector	SF515ES	PIR Motion Detector
SF520	Door/Window Egress Wireless Transmitter & magnet	SF520ES	Door/Window Egress Wireless Transmitter & magnet
SF525	Universal Contact Transmitter for NO maintained input	SF525ES	Universal Contact Transmitter—NO/NC selectable
SF526	Universal Contact Transmitter for NO momentary input		Replaced by SF525ES
		SF525/2ES	Universal Contact Transmitter—1 NC & 1 NO/NC
SF527	Wireless Support Module - 1 required for each SF337C	SF527ES	Wireless Support Module - 1 per SF337C or SF339
SF337C	Waterproof Emergency Switch	SF337C	Waterproof Emergency Switch
SF529A	Check-In/Assistance Station with built-in transmitter	SF529ES	Wireless Check-In/Assistance Station
SF530	Room Station, 1/4" jack with built-in transmitter	SF530ES	Wireless Room Station with 1/4" jack
SF531A	Emergency Switch with built-in transmitter	SF531ES	Wireless Emergency Switch
SF301A	Push-button Call Cord, 1/4" plug, 7 foot cord	SF301A	Push-button Call Cord, 1/4" plug, 7 foot cord
SF301A/10	Push-button Call Cord, 1/4" plug, 10 foot cord	SF301A/10	Push-button Call Cord, 1/4" plug, 10 foot cord
SF301A/20	Push-button Call Cord, 1/4" plug, 20 foot cord	SF301A/20	Push-button Call Cord, 1/4" plug, 20 foot cord
SF301G	Geriatric Call Cord, oxygen use rated, 1/4" plug	SF301G	Geriatric Call Cord, oxygen use rated, 1/4" plug
		SF339	Emergency Switch, locking mushroom push button
IH527	Surface deep single-gang plastic back box for SF527/SF337C assembly or SF530	IH527	Surface deep 1-gang plastic back box for SF527ES/SF337C, SF527ES/SF339, or SF530ES
IH528	Surface single-gang plastic back box for SF529A, SF531A	IH528	Surface 1-gang plastic back box for SF529ES, SF531ES
NC365A	Paging Transmitter/Control Unit	NC369	Paging Transmitter
		CA133	Mo-pole antenna for NC369
NC397A	Alphanumeric Pager	NC399P	Alphanumeric Pager with holster & safety cord
RP397BK	Bungee cord for NC397A - 5 each		
RP397HK	RP397HK Holster belt clip for NC397A - 5 each	RP399H	Replacement holster/belt clip for NC399P
BA501	Replacement Battery for SF501	BA501	Replacement battery for SF501ES, SF501/2ES
BA502	Replacement Battery for SF502	BA502	Replacement battery for SF502ES
BA505	Replacement Battery for SF505, SF515, SF520, SF525, SF526, SF527, SF528		
RP501	Replacement necklace and belt clip for SF501	RP501	Replacement necklace and belt clip for SF501ES
RP503	Small wristband for SF501	RP503	Small wristband for SF501ES, fits wrists 5–6½" around
RP504	Large wristband for SF501	RP504	Large wristband for SF501ES, fits wrists 6½–8" around
SS014	Replacement AC Transformer for NC511, NC512		
ST308K	Replacement reset buttons for SF501 - 10 each	ST308K	Replacement reset buttons for SF501ES - 10 each
		LS501A	Add Frequency Agile transmitters to NC501ES master
		LS501ES	Add Echostream transmitters to NC501A master
		LS501UP	Transfer NC501 database to new NC501ES master